



### 154/154T/154L/154TL Series OMNI-BLOK® Fuse and Holder Assembly



#### Agency Approvals

Recognized under the Components Program of Underwriters Laboratories and Certified by CSA. Approved by METI from 1 through 5 amperes.

| Agency  | Agency File Number | Ampere Range   |
|---|--------------------|--|
|  | E14721             | 154 Fast-Acting Fuse: 0.062A - 10A<br>154 Slo-Blo® Fuse: 0.375A - 7A |
|  | NBK030205-E10480A  | 154 Fast-Acting Fuse: 1A - 1.6A                                      |
|   | NBK030205-E10480B  | 154 Fast-Acting Fuse: 2A - 5A  |
|   | NBK101105-E184655  | 154 Fast-Acting Fuse: 6.3A - 10A                                     |
|   | NBK030205-E10480B  | 154 Slo-Blo® Fuse: 1A - 5A   |

#### Ordering Information

##### With Very Fast-Acting Fuse Installed

| Catalog Number | Ampere Rating (A) | Amp Code | Fuse Furnished* |
|----------------|-------------------|----------|-----------------|
| 0154.062       | 0.062             | .062     | 0451.062        |
| 0154.080       | 0.08              | .080     | 0451.080        |
| 0154.100       | 0.1               | .100     | 0451.100        |
| 0154.125       | 0.125             | .125     | 0451.125        |
| 0154.160       | 0.16              | .160     | 0453.160        |
| 0154.200       | 0.2               | .200     | 0453.200        |
| 0154.250       | 0.25              | .250     | 0453.250        |
| 0154.315       | 0.315             | .315     | 0453.315        |
| 0154.375       | 0.375             | .375     | 0453.375        |
| 0154.400       | 0.4               | .400     | 0453.400        |
| 0154.500       | 0.5               | .500     | 0453.500        |
| 0154.630       | 0.63              | .630     | 0453.630        |
| 0154.750       | 0.75              | .750     | 0453.750        |
| 0154.800       | 0.8               | .800     | 0453.800        |
| 0154001.       | 1                 | 001.     | 0453001.        |
| 01541.25       | 1.25              | 1.25     | 04531.25        |
| 015401.5       | 1.5               | 01.5     | 045301.5        |
| 015401.6       | 1.6               | 01.6     | 045301.6        |
| 0154002.       | 2                 | 002.     | 0453002.        |
| 015402.5       | 2.5               | 02.5     | 045302.5        |
| 0154003.       | 3                 | 003.     | 0453003.        |
| 01543.15       | 3.15              | 3.15     | 04533.15        |
| 015403.5       | 3.5               | 03.5     | 045303.5        |
| 0154004.       | 4                 | 004.     | 0453004.        |
| 0154005.       | 5                 | 005.     | 0453005.        |
| 015406.3       | 6.3               | 06.3     | 045306.3        |
| 0154007.       | 7                 | 007.     | 0453007.        |
| 0154008.       | 8                 | 008.     | 0453008.        |
| 0154010.       | 10                | 010.     | 0453010.        |

#### Description

The RoHS compliant 154 Series OMNI-BLOK® Fuse and Holder Assembly offers a solution for efficient installation and easy replacement of miniature Nano<sup>2</sup>® surface mount fuses. Offered in a tape and reel package, this fuse and holder combination can be installed on a PC board as an efficient single step. Fuse replacement can be accomplished without exposing the PC board to the detrimental effects of solder heat.

The fuse holder unit may be sold as a stand-alone item, shipped in bulk quantity (not pre-packaged in tape and reel cartridges) using part number 155900. Please contact Littelfuse for additional information.

#### Features

- Easy fuse replacement
- Miniature size
- RoHS compliant and Halogen Free
- Very Fast-Acting and Time-Lag options available
- Holder sized to fit a range of Nano<sup>2</sup>® type fuses
- Low fuse temperature re-rating
- Wide range of current rating available
  - Fast-Acting: 62mA - 10A
  - Slo-Blo®: 375mA - 5A
- Wide operating temperature range
- Heat-resistant fuseholder, UL94 V-0
- 260°C reflow capable fuseholder

##### With Slo-Blo® Fuse Installed

| Catalog Number | Ampere Rating (A) | Amp Code | Fuse Furnished* |
|----------------|-------------------|----------|-----------------|
| 154.375 T      | 0.375             | .375     | 0454.375        |
| 154.500 T      | 0.5               | .500     | 0454.500        |
| 154.750 T      | 0.75              | .750     | 0454.750        |
| 154001. T      | 1                 | 001.     | 0454001.        |
| 15401.5 T      | 1.5               | 01.5     | 045401.5        |
| 154002. T      | 2                 | 002.     | 0454002.        |
| 15402.5 T      | 2.5               | 02.5     | 045402.5        |
| 154003. T      | 3                 | 003.     | 0454003.        |
| 15403.5 T      | 3.5               | 03.5     | 045403.5        |
| 154004. T      | 4                 | 004.     | 0454004.        |
| 154005. T      | 5                 | 005.     | 0454005.        |
| 154007. T      | 7                 | 007.     | 0454007.        |

\* The 453 and 454 Series fuses identified above have silver-plated end caps, designed to accommodate solder reflow processes:

For 453 Series fuse replacement, either 451, 453 or 448 Series may be used.


For 454 Series fuse replacement, either 452, 454 or 449 Series may be used.

For detailed operating characteristic and performance information for each of the fuse series mentioned above, please refer to their respective data available online at [www.littelfuse.com](http://www.littelfuse.com).

\*\* 155900 is UR recognized and rated 125V, 10A.

### Soldering Parameters


|  |                                    |                         |
|--|------------------------------------|-------------------------|
| Reflow Condition                                       |                                    | Pb – Free assembly      |
| Pre Heat   | - Temperature Min ( $T_{s(min)}$ ) | 150°C                   |
|  | - Temperature Max ( $T_{s(max)}$ ) | 200°C                   |
|  | - Time (Min to Max) ( $t_s$ )      | 60 – 120 seconds        |
| Average Ramp-up Rate (Liquidus Temp ( $T_L$ ) to peak) |                                    | 5°C/second max.         |
| $T_{s(max)}$ to $T_L$ - Ramp-up Rate                   |                                    | 5°C/second max.         |
| Reflow   | - Temperature ( $T_L$ ) (Liquidus) | 217°C                   |
|  | - Temperature ( $t_L$ )            | 60 – 90 seconds         |
| Peak Temperature ( $T_p$ )                             |                                    | 260 <sup>+0/-5</sup> °C |
| Time within 5°C of actual peak Temperature ( $t_p$ )   |                                    | 20 – 40 seconds         |
| Ramp-down Rate   |                                    | 5°C/second max.         |
| Time 25°C to peak Temperature ( $T_p$ )                |                                    | 8 minutes max.          |
| Do not exceed  |                                    | 260°C                   |




### Product Characteristics

|                              |                |
|------------------------------|----------------|
| <b>Operating Temperature</b> | -55°C to 125°C |
|------------------------------|----------------|

### Dimensions



### Part Numbering System



**Example:**  
 1.5 amp Fast-acting product is 0154**01.5**DR.  
 1.5 amp Time-lag product is 0154**01.5**DRT.  
 (1 amp product shown above).

### Packaging

| Packaging Option | Packaging Specification        | Quantity | Quantity & Packaging Code |
|------------------|--------------------------------|----------|---------------------------|
| Reel Pack        | EIA RS-481-2 (IEC 286, part 3) | 1500     | DR                        |

### Additional Information



Datasheet



Resources



Samples

Компания «Океан Электроники» предлагает заключение долгосрочных отношений при поставках импортных электронных компонентов на взаимовыгодных условиях!

Наши преимущества:

- Поставка оригинальных импортных электронных компонентов напрямую с производств Америки, Европы и Азии, а так же с крупнейших складов мира;
- Широкая линейка поставок активных и пассивных импортных электронных компонентов (более 30 млн. наименований);
- Поставка сложных, дефицитных, либо снятых с производства позиций;
- Оперативные сроки поставки под заказ (от 5 рабочих дней);
- Экспресс доставка в любую точку России;
- Помощь Конструкторского Отдела и консультации квалифицированных инженеров;
- Техническая поддержка проекта, помощь в подборе аналогов, поставка прототипов;
- Поставка электронных компонентов под контролем ВП;
- Система менеджмента качества сертифицирована по Международному стандарту ISO 9001;
- При необходимости вся продукция военного и аэрокосмического назначения проходит испытания и сертификацию в лаборатории (по согласованию с заказчиком);
- Поставка специализированных компонентов военного и аэрокосмического уровня качества (Xilinx, Altera, Analog Devices, Intersil, Interpoint, Microsemi, Actel, Aeroflex, Peregrine, VPT, Syfer, Eurofarad, Texas Instruments, MS Kennedy, Miteq, Cobham, E2V, MA-COM, Hittite, Mini-Circuits, General Dynamics и др.);

Компания «Океан Электроники» является официальным дистрибьютором и эксклюзивным представителем в России одного из крупнейших производителей разъемов военного и аэрокосмического назначения «JONHON», а так же официальным дистрибьютором и эксклюзивным представителем в России производителя высокотехнологичных и надежных решений для передачи СВЧ сигналов «FORSTAR».



## JONHON

«JONHON» (основан в 1970 г.)

Разъемы специального, военного и аэрокосмического назначения:

(Применяются в военной, авиационной, аэрокосмической, морской, железнодорожной, горно- и нефтедобывающей отраслях промышленности)

«FORSTAR» (основан в 1998 г.)

ВЧ соединители, коаксиальные кабели, кабельные сборки и микроволновые компоненты:

(Применяются в телекоммуникациях гражданского и специального назначения, в средствах связи, РЛС, а так же военной, авиационной и аэрокосмической отраслях промышленности).



Телефон: 8 (812) 309-75-97 (многоканальный)

Факс: 8 (812) 320-03-32

Электронная почта: [ocean@oceanchips.ru](mailto:ocean@oceanchips.ru)

Web: <http://oceanchips.ru/>

Адрес: 198099, г. Санкт-Петербург, ул. Калинина, д. 2, корп. 4, лит. А